

# DS9100 Touch and Hold Probe Stampings

#### www.maxim-ic.com

### **FEATURES**

- Compact two-piece, all-metal receptacle for F5 MicroCan
- Accepts two-thirds of the MicroCan (onethird of MicroCan will extend out)
- Allows reading <u>iButtons</u>® with either momentary or dwelled contact
- Outer ring will hold MicroCan for dwelled contact
- Two options for data contact: cantilever (DS9100B) or coiled spring (DS9100C)
- >10000 insertion/withdrawal cycles with no performance degradation
- Redundancy of contacts and high contact force ensure reliability
- Probe withstands high temperatures required for PCB solder reflow operations
- Material is stainless steel with selective tinlead plating for optimal solderability to printed circuit board
- Cleaning fluids drain freely for quick clean up

### **ORDERING INFORMATION**

| PART      | DESCRIPTION                  |  |
|-----------|------------------------------|--|
| DS9100-A+ | Outer Contact (Ground)       |  |
| DS9100-B+ | Center Contact Cantilever    |  |
|           | (Data)                       |  |
| DS9100-C+ | Center Contact Coiled Spring |  |
|           | (Data)                       |  |

+Denotes a lead(Pb)-free/RoHS-compliant package.

iButton is a registered trademark of Maxim Integrated Products, Inc.

### DS9100A WITH DS9100B





Dimensions are in millimeters

### DS9100C WITH CORRECT ORIENTATION TO SOLDER PAD



## DESCRIPTION

The DS9100 Touch and Hold Probe Stampings' function is similar to the DS9098 <u>i</u>Button Retainer. An F5 MicroCan will fit completely into the DS9098, but the flange and about one-third of the can will extend out if pressed into the DS9100. As a probe, the DS9100A together with the coiled spring DS9100C allows reading <u>i</u>Buttons on contact. With additional pressure, the stiff springs of the DS9100A's outer ring will deflect and grip the MicroCan sufficiently to provide a continuous contact to both the can rim (ground) and the can lid (data). If reading on contact is not required, the cantilever type center contact DS9100B can be used rather than the DS9100C.

# PRINTED CIRCUIT BOARD LAYOUTS







Compatible PCB layout. Good for either center part DS9100B or DS9100C



Additional diminsions for ground contact.





Side A









Center piece optimized for coiled spring DS9100C

Dimensions are in millimeters.

The DS9100 stampings are mounted on Side A of the printed circuit board.

| REVISION HISTORY |  |                  |
|------------------|--|------------------|
| REVISION<br>DATE | DESCRIPTION  | PAGES<br>CHANGED |
| 8/09             | Updated the PART numbers in the <i>Ordering Information</i> table to indicate lead(Pb)-free/RoHS-compliant packages. | 1                |

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

#### Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600

© 2009 Maxim Integrated Products

3 of 3